WaterVac 100 Vacuum Filtration System



Features

► Save 70% bench space

The compact design of WaterVac 100 vacuum filtration system can save much bench space by simplifying procedure and tools needed in membrane filtration method.

Improve operation time

Direct drainage design saves a lot of time to empty waste bottle and make the filtration more efficient.

Versatile

Replaceable funnel adaptor design makes WaterVac 100 compatible with various kinds of filter holder.

International certification

CE certification

One-Year Warranty

Applications

- Microbiological test
- ► Vacuum filtration

WaterVac 100 - MS WaterVac 100 WaterVac 100 REJENSER





Improve operation time

Compatible with various kinds of adaptor and filter holder

Ordering Information

190100-01(02)

WaterVac 100, Vacuum Filtration System with AC100~240V adaptor, US plug (EU plug)

190110-01(02)

WaterVac 100 - MS, Vacuum Filtration System with No. 8 stopper funnel adaptor, AC100~240V adaptor, US plug (EU plug)

200300-01

MF 3, 300 ml Magnetic Filter Holder with lid kit

200500-01

MF 5, 500 ml Magnetic Filter Holder with lid kit

Specification

Model	WaterVac 100	
Power	DC12V, 1.0A	
Max. vacuum	313 mbar	
Max. liquid flow rate	0.5 L/min	
Motor	12W Brushless DC Motor	
Hose barb	ID6	
Material contact with filtrate	SS316, FKM, Silicone, PP, PA66	
Weight	1.16 Kg	
Dimension (LxWxH)	17 x 12 x 9.6 cm	
	WaterVac 100 - MS	
Number of branch	1	
Adaptor	No. 8 stopper	
Filter holder	MF 3 / MF 5, 300 ml / 500 ml magnetic filter holder (optional)	



WaterVac 100 Vacuum Filtration System



Features

► Save 70% bench space

The compact design of WaterVac 100 vacuum filtration system can save much bench space by simplifying procedure and tools needed in membrane filtration method.

Improve operation time

Direct drainage design saves a lot of time to empty waste bottle and make the filtration more efficient.

Versatile

Replaceable funnel adaptor design makes WaterVac 100 compatible with various kinds of filter holder.

Compatible with Rocker SF funnel

WaterVac 100 - MB can accept Rocker SF funnel - 100 / 300 / 500 ml. SF funnel is made of SS316 stainless steel which can be fast sterilized by flame.

▶ International certification

CE certification

One-Year Warranty

Applications

- ► Microbiological test
- ► Vacuum filtration

Ordering Information

190100-01(02)

WaterVac 100, Vacuum Filtration System with AC100~240V adaptor, US plug (EU plug)

190120-01(02)

WaterVac 100 - MB, Vacuum Filtration System with Rocker SF funnel adaptor, AC100~240V adaptor, US plug (EU plug)

190121-01(02)

WaterVac 101 - MB, Vacuum Filtration System with Rocker SF funnel adaptor, 100 ml SF funnel, AC100~240V adaptor, US plug (EU plug)

180100-01

SF, 100 ml Stainless Steel Funnel

180100-03

SF, 300 ml Stainless Steel Funnel

180100-05

SF, 500 ml Stainless Steel Funnel

WaterVac 100 - MB



WaterVac 101 - MB



Specification

Model	WaterVac 100	
Power	DC12V, 1.0A	
Max. vacuum	313 mbar	
Max. liquid flow rate	0.5 L/min	
Motor	12W Brushless DC Motor	
Hose barb	ID6	
Material contact with filtrate	SS316, FKM, Silicone, PP, PA66	
Weight	1.16 Kg	
Dimension (LxWxH)	17 x 12 x 9.6 cm	
	WaterVac 100 - MB	WaterVac 101 - MB
Number of branch	1	1
Adaptor	Spin-lock design	Spin-lock design
Funnel	SF stainless steel funnel, 100 / 300 /500 ml (optional)	SF stainless steel funnel, 100 ml (standard)



How to order?

You can select Combination A, B or C





WaterVac 100 - MB Vacuum Filtraion System (190120-01/02) (US plug / EU plug)





WaterVac 100 - MS Vacuum Filtraion System (190110-01/02) (US plug / EU plug)







SF Stainless Steel Funnel SF Stainless Steel Funnel SF Stainless Steel Funnel (180100-01)



(180100-03)



(180100-05)



Stainless Steel Cover for SF 100 ml funnel (180100-11)



Stainless Steel Cover for SF 300 / 500 ml funnel (180100-13)



Rocker, 300 ml MF 3, Magnetic Filter Holder (200300-01)




Rocker, 500 ml MF 5, Magnetic Filter Holder (200500-01)

to complete your order



Customized Design

We can offer customized adaptor for your funnel





Sartorius, 100 ml / 250 ml Microsart® disposable plastic funnel (16A07--10-----N/ 16A07--25-----N)





SS316 Adaptor for Sartorius disposable plastic funnel (190100-74)



Millipore, 100 ml / 250 ml Microfil® disposable plastic funnel (MIHAWG100 / MIHAWG250)

+



SS316 Adaptor for Millipore disposable plastic funnel (190100-73)



Pall, 100 ml / 250 ml Sentino® disposable plastic funnel (4870 / 4871)

+



SS316 Adaptor for Pall disposable plastic funnel (190100-75)



Silicone Tube Ø 4.2 x 8 mm, 200 cm (199100-68)





SS316 Hose barb for silicone tube (ID4~ID8) (190100-76)

* SS316 adaptor is only available for above-mentioned disposable funnels.

